

WZAD 70/95**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	Auxiliary connection (terminal), Number of connections: 1
Order No.	1066000000
Type	WZAD 70/95
GTIN (EAN)	4008190017064
Qty.	10 pc(s).

WZAD 70/95

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	10 mm	Depth (inches)	0.394 inch
Height	39.61 mm	Height (inches)	1.559 inch
Width	19.7 mm	Width (inches)	0.776 inch
Net weight	6.05 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	tinned copper	Colour	Silver grey
----------	---------------	--------	-------------

System specifications

Version	Additional connection	Number of levels	1
Number of clamping points per level	1		

Additional technical data

Explosion-tested version	No	Installation advice	Feed-through (bushing), Direct mounting
Type of fixing	Snap-on		

Conductors for clamping (rated connection)

Number of connections	1
-----------------------	---

Dimensions

Pitch in mm (P)	20 mm
-----------------	-------

General

Installation advice	Feed-through (bushing), Direct mounting
---------------------	---

Rating data

Rated voltage	800 V	Rated DC voltage	800 V
Rated current	32 A		

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-08

Approvals

ROHS	Conform
------	---------

WZAD 70/95

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	