

**WZAF 70****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The additional connection enables a separate voltage tap. This can be used, for example, for the emergency power supply before the main switch or simply as an additional connection within the application.

**General ordering data**

Version	Auxiliary connection (terminal)
Order No.	<a href="#">1066200000</a>
Type	WZAF 70
GTIN (EAN)	4008190169831
Qty.	10 pc(s).

## WZAF 70

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	10 mm	Depth (inches)	0.394 inch
Height	30 mm	Height (inches)	1.181 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	8.3 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Material	tinned copper	Colour	Silver grey
----------	---------------	--------	-------------

## System specifications

Version	Additional connection
---------	-----------------------

## Additional technical data

Explosion-tested version	No	Installation advice	Feed-through (bushing), Direct mounting
Type of fixing	Plugged		

## Dimensions

Pitch in mm (P)	27 mm
-----------------	-------

## General

Installation advice	Feed-through (bushing), Direct mounting
---------------------	-----------------------------------------

## Rating data

Rated current	32 A
---------------	------

## Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-08

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>