


AP VSSC4 LB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

End plates (AP) for the VSSC product series in light blue and black

General ordering data

Version	VSSC, End plate
Order No.	1067240000
Type	AP VSSC4 LB
GTIN (EAN)	4032248999873
Qty.	50 pc(s).

AP VSSC4 LB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	58.5 mm	Depth (inches)	2.303 inch
Height	76 mm	Height (inches)	2.992 inch
Width	1.5 mm	Width (inches)	0.059 inch
Net weight	4.22 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70
Humidity	5...96 %		

General data

Colour	Light Blue	Design	miscellaneous
UL 94 flammability rating	V-0	Version	End plate

Connection data

Type of connection	Screw connection
--------------------	------------------

Classifications

ETIM 6.0	EC000490	ETIM 7.0	EC000490
ETIM 8.0	EC000490	ETIM 9.0	EC000490
ECLASS 9.1	27-13-92-90	ECLASS 11.0	27-13-08-92
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

Tender specification sheets

Long specification	End plate for VSSC4	Short specification	End plate for VARITECTOR VSSC4
--------------------	---------------------	---------------------	--------------------------------

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format