

IE-PI-HYB-10P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

General ordering data

Version	Insert, for plug insert, Hybrid
Order No.	1068990000
Type	IE-PI-HYB-10P
GTIN (EAN)	4032248823963
Qty.	1 pc(s).

IE-PI-HYB-10P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	16.29 g
------------	---------

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

General data

Category	Cat.5 (ISO/IEC 11801)	Connection 1	Hybrid (Q10)
Connection 2	Crimp	Housing main material	Nickel silver, PA 66
Insulation cross-section, max.	2.2 mm	Insulation cross-section, min.	1 mm
Plugging cycles	500	Protection degree	IP67 with housing
Shielding	360°; all-round enclosure	Wire connection cross section, finely stranded, max.	0.75 mm ²
Wire connection cross section, finely stranded, min.	0.08 mm ²	Wire cross-section, finely stranded, max. (AWG)	AWG 20
Wire cross-section, finely stranded, min. (AWG)	AWG 27		

Electrical properties

Contact resistance	≤ 5 mΩ	Rated current	3 A per contact
Rated voltage	24 V	Volume resistance	<10 mΩ

General standards

Certificate no. (cULus)	E316369
-------------------------	---------

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ECLASS 9.0	27-44-03-90	ECLASS 9.1	27-44-09-90
ECLASS 10.0	27-44-03-90	ECLASS 11.0	27-44-03-90
ECLASS 12.0	27-44-03-90	ECLASS 13.0	27-44-03-90

Important note

Product information	Hybrid, 10-pole. Inserts for plug-in connectors Variant 14
---------------------	--

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

IE-PI-HYB-10P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	DUXR.E316369 PROFINET Manufacturer's Declaration
Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Designation key / Type key
Catalogues	Catalogues in PDF-format
Brochures	MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN


IE-PI-HYB-10P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



IE-PI-HYB-10P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Hybrid

Hybrid, 10-pole. Inserts for plug-in connectors Variant 14



General ordering data

Type	IE-PIC-HYB-S-0,2-300	Version
Order No.	1135150000	Crimp contact, for plug insert, Hybrid
GTIN (EAN)	4032248915347	
Qty.	300 pc(s).	
Type	IE-PIC-HYB-S-0,5-300	Version
Order No.	1096180000	Crimp contact, for plug insert, Hybrid
GTIN (EAN)	4032248869152	
Qty.	300 pc(s).	
Type	IE-PIC-HYB-S-0,75-300	Version
Order No.	1068950000	Crimp contact, for plug insert, Hybrid
GTIN (EAN)	4032248823109	
Qty.	300 pc(s).	

Crimping tools



Crimping tools for Weidmüller contacts for RSV and DSTV-HD systems

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF HYB	Version
Order No.	1119580000	Pressing tool, Crimping tool for contacts, 0.08mm², 1mm²,
GTIN (EAN)	4032248900626	FoderBcrimp
Qty.	1 pc(s).	