

WAP 2.5-10 VI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

Version	End plate (terminals), 56 mm x 1.5 mm, violet
Order No.	1072210000
Type	WAP 2.5-10 VI
GTIN (EAN)	4008190455460
Qty.	50 pc(s).

WAP 2.5-10 VI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	33.5 mm	Depth (inches)	1.319 inch
Height	56 mm	Height (inches)	2.205 inch
Width	1.5 mm	Width (inches)	0.059 inch
Net weight	2.58 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	Wemid	Colour	violet
UL 94 flammability rating	V-0		

System specifications

Version	End plate
---------	-----------

Additional technical data

Installation advice	Direct mounting	Snap-on	No
---------------------	-----------------	---------	----

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ETIM 9.0	EC000886
ECLASS 9.1	27-14-11-33	ECLASS 10.0	27-14-11-33
ECLASS 11.0	27-14-11-33	ECLASS 12.0	27-14-11-33
ECLASS 13.0	27-25-03-01		

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Confirmation of Standards EN 45545-2_2020-10
Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format