

KSWF M50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|---------------------|---|
| Version | KSWF (flat gasket - vulcanised fibre), Sealing ring, M 50, Vulcanized fibre |
| Order No. | 1076720000 |
| Type | KSWF M50 |
| GTIN (EAN) | 4032248838646 |
| Qty. | 25 pc(s). |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2024-08-31 |
| Alternative product | 0899780000 |

KSWF M50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Height | 1.5 mm | Height (inches) | 0.059 inch |
| Net weight | 2.68 g | | |

Temperatures

| | |
|-----------------------|----------------|
| Operating temperature | -40 °C...95 °C |
|-----------------------|----------------|

General information

| | | | |
|-----------------------------------|------------------|-----------------------------------|--------|
| Cable glands | M 50 | Diameter of sealing ring | 65 mm |
| External thread | M 50 | Internal thread | M 50 |
| Material | Vulcanized fibre | Number of wires | 1 |
| Operating temperature range, max. | 95 °C | Operating temperature range, min. | -40 °C |
| Pitch of thread | 1.5 mm | Silicone | No |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001181 | ETIM 7.0 | EC001181 |
| ETIM 8.0 | EC001181 | ETIM 9.0 | EC001181 |
| ECLASS 9.0 | 27-43-03-19 | ECLASS 9.1 | 27-14-44-90 |
| ECLASS 10.0 | 27-43-03-19 | ECLASS 11.0 | 27-43-03-19 |
| ECLASS 12.0 | 27-43-03-19 | ECLASS 13.0 | 27-43-03-19 |
| ECLASS 14.0 | 27-43-03-19 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
| Brochures | |

KSWF M50

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

