

**KSWF M75****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	KSWF (flat gasket - vulcanised fibre), Sealing ring, M 75, Vulcanized fibre
Order No.	<a href="#">1076740000</a>
Type	KSWF M75
GTIN (EAN)	4032248838660
Qty.	25 pc(s).
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2024-08-31

**KSWF M75****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	1.5 mm	Height (inches)	0.059 inch
Net weight	3.4 g		

**Temperatures**

Operating temperature	-40 °C...95 °C
-----------------------	----------------

**General information**

Cable glands	M 75	Diameter of sealing ring	90.5 mm
External thread	M 75	Internal thread	M 75
Material	Vulcanized fibre	Number of wires	1
Operating temperature range, max.	95 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Silicone	No

**Classifications**

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ETIM 9.0	EC001181
ECLASS 9.0	27-43-03-19	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-43-03-19	ECLASS 11.0	27-43-03-19
ECLASS 12.0	27-43-03-19	ECLASS 13.0	27-43-03-19
ECLASS 14.0	27-43-03-19		

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## KSWF M75

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

