

**WQB PEN 16N****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

A PEN bridge joins separate PE and N conductors into one PEN conductor.

**General ordering data**

|            |   |
|------------|---|
| Version    | Cross-connector (terminal), when screwed in, Number of poles: 2, Pitch in mm (P): 12.00, Insulated: No, 76 A, Silver grey |
| Order No.  | <a href="#">1079600000</a>  |
| Type       | WQB PEN 16N   |
| GTIN (EAN) | 4008190370107   |
| Qty.       | 10 pc(s).   |

**WQB PEN 16N****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 1.2 mm   | Depth (inches)  | 0.047 inch |
| Height     | 21.09 mm | Height (inches) | 0.83 inch  |
| Width      | 17.6 mm  | Width (inches)  | 0.693 inch |
| Net weight | 3.4 g    |                 |            |

**Temperatures**

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

**Material data**

|          |               |        |             |
|----------|---------------|--------|-------------|
| Material | tinned copper | Colour | Silver grey |
|----------|---------------|--------|-------------|

**System specifications**

|         |                 |
|---------|-----------------|
| Version | Cross-connector |
|---------|-----------------|

**Additional technical data**

|                          |                 |                |                 |
|--------------------------|-----------------|----------------|-----------------|
| Explosion-tested version | No              | Type of fixing | when screwed in |
| Type of mounting         | when screwed in |                |                 |

**Cross-connector**

|                           |      |      |                 |
|---------------------------|------|------|-----------------|
| Rated current, multi-pole | 76 A | Type | Cross-connector |
|---------------------------|------|------|-----------------|

**Dimensions**

|                 |       |
|-----------------|-------|
| Pitch in mm (P) | 12 mm |
|-----------------|-------|

**General**

|                 |   |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

**Rating data**

|               |      |
|---------------|------|
| Rated current | 76 A |
|---------------|------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ECLASS 9.0  | 27-14-11-40 | ECLASS 9.1  | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

**Environmental Product Compliance**

|            |   |
|------------|---|
| REACH SVHC | / |
|------------|---|

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### WQB PEN 16N

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>                 |
| Engineering Data   | <a href="#">Zuken E3.S</a>                      |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |
| Brochures          |   |