

HDC IP68 06B SS 2M25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**IP68**

The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

General ordering data

| | |
|------------|---|
| Version | HDC enclosures, Size: 3, Protection degree: IP66 (in plugged condition), IP68 (in plugged condition), Base housing, Clamping yoke connection, Standard, Size of cable entries: M 25 |
| Order No. | 1081240000 |
| Type | HDC IP68 06B SS 2M25 |
| GTIN (EAN) | 4032248877201 |
| Qty. | 1 pc(s). |

HDC IP68 06B SS 2M25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|-----------------------------|--------|----------------------------|------------|
| Depth | 156 mm | Depth (inches) | 6.142 inch |
| Height | 101 mm | Height (inches) | 3.976 inch |
| Width | 80 mm | Width (inches) | 3.15 inch |
| Mounting dimension - height | 60 mm | Mounting dimension - width | 127 mm |
| Net weight | 866 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -50 °C ... 125 °C |
|-------------------|-------------------|

Dimensions

| | | | |
|----------------------|-----------|----------------------|--------|
| Cable entry | w. thread | Height of housing B | 101 mm |
| Hole pitch length A2 | 127 mm | Total length housing | 156 mm |

General data

| | | | |
|-------------------|--|-----------------------|-------------------|
| EMC housings | Yes | Housing main material | diecast aluminium |
| Protection degree | IP66 (in plugged condition), IP68 (in plugged condition) | Surface finish | Powder coating |

Version

| | | | |
|------------------------------|--------------------------|--------------------------------|--------------------|
| BG | 3 | Cable entry | w. thread |
| Clamp version | Clamping yoke connection | Colour (RAL) | RAL 9011, RAL 9005 |
| Design | Standard | Design of housing | Base housing |
| Design of locking system | Clamping yoke connection | Internal thread | M 25 |
| Number of cable entry on top | 0 | Number of cable entry sideways | 2 |
| Sealing | Silicone | Size | 3 |
| Size of cable entries | M 25 | Suitable for ModuPlug® | Yes |
| Top part/bottom part/lid | lower part | Type | Base housing |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000437 | ETIM 7.0 | EC000437 |
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ECLASS 9.0 | 27-44-02-02 | ECLASS 9.1 | 27-44-02-02 |
| ECLASS 10.0 | 27-44-02-02 | ECLASS 11.0 | 27-44-02-02 |
| ECLASS 12.0 | 27-44-02-02 | ECLASS 13.0 | 27-44-02-02 |
| ECLASS 14.0 | 27-44-02-02 | | |

| | |
|---------------------|-------------------------|
| Substance | Acetone |
| Chemical resistance | Resistant |
| Substance | Diesel oil |
| Chemical resistance | Unstable |
| Substance | Ethyl alcohol |
| Chemical resistance | Resistant |
| Substance | Transmission oil |
| Chemical resistance | Conditionally resistant |
| Substance | Hydraulic oil |

HDC IP68 06B SS 2M25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

| | |
|---------------------|-------------------------|
| Chemical resistance | Conditionally resistant |
| Substance | Petroleum benzine |
| Chemical resistance | Unstable |
| Substance | Sweat |
| Chemical resistance | Conditionally resistant |
| Substance | Premium gasoline |
| Chemical resistance | Unstable |
| Substance | Water |
| Chemical resistance | Resistant |
| Substance | UV |
| Chemical resistance | Resistant |
| Substance | Ozone |
| Chemical resistance | Resistant |

Environmental Product Compliance

| | |
|------------------------|--|
| REACH SVHC | / |
| Chemical resistance | de.myview.objectmodel.impl.BlockImpl@71b7c271 de.myview.objectmodel.impl.BlockImpl@38676044 de.myview.objectmodel.impl.BlockImpl@57ddd53 de.myview.objectmodel.impl.BlockImpl@693ddf58 de.myview.objectmodel.impl.BlockImpl@26d63c44 de.myview.objectmodel.impl.BlockImpl@25301d9a de.myview.objectmodel.impl.BlockImpl@1cbe7b2a de.myview.objectmodel.impl.BlockImpl@1bfea0fa de.myview.objectmodel.impl.BlockImpl@c5d9bdd de.myview.objectmodel.impl.BlockImpl@29a48b01 de.myview.objectmodel.impl.BlockImpl@462cc234 |
| RoHS Compliance Status | Compliant without exemption |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads


| | |
|---|--|
| Approval/Certificate/Document of Conformity | Manufacturer's declaration |
| Engineering Data | CAD data – STEP |
| Product Change Notification | 20220214 Technical change to HDC housings 20220214 Technische Änderung bei HDC-Gehäusen |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN FL FIELDWIRING EN |

HDC IP68 06B SS 2M25

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HDC IP68 06B SS 2M25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****IP68 O-ring seals**

We offer a variety of accessories, including seals, to accompany the housings.

Because of the excellent sealing, you can achieve the best seal possible with our housings.

Extensive testing has confirmed it – RockStar® remains impermeable to water to a depth of 50 metres. This allows you to use heavy-duty connectors in environments which previously required fixed-wire installation.

General ordering data

| | | |
|------------|----------------------------|-------------------------------------|
| Type | HDC DG 06B IP68 | Version |
| Order No. | 1987490000 | Accessories, Enclosures accessories |
| GTIN (EAN) | 4050118379198 | |
| Qty. | 1 pc(s). | |