

HDC IP68 10B AS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**IP68**

The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

General ordering data

Version	HDC enclosures, Size: 4, Protection degree: IP69K, IP66 (in plugged condition), IP68 (in plugged condition), Bulkhead housing, Clamping yoke connection, Standard
Order No.	1081520000
Type	HDC IP68 10B AS
GTIN (EAN)	4032248844272
Qty.	1 pc(s).

HDC IP68 10B AS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	29.5 mm	Height (inches)	1.161 inch
Width	58 mm	Width (inches)	2.283 inch
Mounting dimension - height	32 mm	Mounting dimension - width	83 mm
Net weight	170 g		

Temperatures

Limit temperature	-50 °C ... 125 °C
-------------------	-------------------

Dimensions

Hole pitch length A2	83 mm	Total length housing	144 mm
----------------------	-------	----------------------	--------

General data

EMC housings	Yes	Housing main material	diecast aluminium
Protection degree	IP69K, IP66 (in plugged condition), IP68 (in plugged condition)	Surface finish	Powder coating

Version

BG	4	Clamp version	Clamping yoke connection
Colour (RAL)	RAL 9011, RAL 9005	Design	Standard
Design of housing	Bulkhead housing	Design of locking system	Clamping yoke connection
Sealing	Silicone	Size	4
Suitable for ModuPlug®	Yes	Top part/bottom part/lid	lower part
Type	Bulkhead (feed-through)		

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ECLASS 9.0	27-44-02-02	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-02	ECLASS 11.0	27-44-02-02
ECLASS 12.0	27-44-02-02	ECLASS 13.0	27-44-02-02

Substance	Acetone
Chemical resistance	Resistant
Substance	Diesel oil
Chemical resistance	Unstable
Substance	Ethyl alcohol
Chemical resistance	Resistant
Substance	Transmission oil
Chemical resistance	Conditionally resistant
Substance	Hydraulic oil
Chemical resistance	Conditionally resistant
Substance	Petroleum benzine
Chemical resistance	Unstable

HDC IP68 10B AS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Substance	Sweat
Chemical resistance	Conditionally resistant
Substance	Premium gasoline
Chemical resistance	Unstable
Substance	Water
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Resistant
Substance	Ozone
Chemical resistance	Resistant

Environmental Product Compliance

REACH SVHC

/

Chemical resistance

de.myview.objectmodel.impl.BlockImpl@6e255507 de.myview.objectmodel.impl.BlockImpl@139e8ffc
 de.myview.objectmodel.impl.BlockImpl@230c8f8c de.myview.objectmodel.impl.BlockImpl@4236ca7
 de.myview.objectmodel.impl.BlockImpl@40ea8c49 de.myview.objectmodel.impl.BlockImpl@27ec0ac7
 de.myview.objectmodel.impl.BlockImpl@60db8159 de.myview.objectmodel.impl.BlockImpl@7f828fb1
 de.myview.objectmodel.impl.BlockImpl@6b1edccc de.myview.objectmodel.impl.BlockImpl@2c63495a
 de.myview.objectmodel.impl.BlockImpl@108ed4c6

Important note

Product information

When mounting the housings, make sure that the flat gasket is correctly seated.

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[Manufacturer's declaration](#)

Engineering Data

[CAD data – STEP](#)

Product Change Notification

[20220214 Technical change to HDC housings](#)
[20220214 Technische Änderung bei HDC-Gehäusen](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)
[FL FIELDWIRING EN](#)

HDC IP68 10B AS

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



HDC IP68 10B AS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****IP68 O-ring seals**

We offer a variety of accessories, including seals, to accompany the housings.

Because of the excellent sealing, you can achieve the best seal possible with our housings.

Extensive testing has confirmed it – RockStar® remains impermeable to water to a depth of 50 metres. This allows you to use heavy-duty connectors in environments which previously required fixed-wire installation.

General ordering data

Type	HDC DG 10B IP68	Version
Order No.	1987510000	Accessories, Enclosures accessories
GTIN (EAN)	4050118379228	
Qty.	1 pc(s).	

Flange seals

We offer a variety of accessories, including seals, to accompany the housings.

Because of the excellent sealing, you can achieve the best seal possible with our housings.

Extensive testing has confirmed it – RockStar® remains impermeable to water to a depth of 50 metres. This allows you to use heavy-duty connectors in environments which previously required fixed-wire installation.

General ordering data

Type	HDC FLDG 10B IP68	Version
Order No.	1987500000	Accessories, Enclosures accessories
GTIN (EAN)	4050118379211	
Qty.	1 pc(s).	