

THM WO 50.8/150 RT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 39.7 mm, 50.8 x 150 mm, red
Order No.	1109170000
Type	THM WO 50.8/150 RT
GTIN (EAN)	4032248885619
Qty.	1 pc(s).

THM WO 50.8/150 RT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	50.8 mm	Height (inches)	2 inch
Width	150 mm	Width (inches)	5.905 inch
Net weight	622 g		

Temperatures

Operating temperature range	-40...125 °C
-----------------------------	--------------

General data

Adhesive	Polyacrylate adhesive	
Colour	red	
Halogen	No	
Material	Polyester film	
Material colour according to resistance code	2	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Label reel
Number per roll	500	
Operating temperature range	-40...125 °C	
Operating temperature range, max.	125 °C	
Operating temperature range, min.	-40 °C	
Size of labelling field	25.4 x 50.8 mm	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Version	Self-adhesive	
Width	150 mm	

Conductor and cable markers

Conductor O.D.	39.7 mm	Conductor O.D., max.	39.7 mm
Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	0.75 mm ²
Cross-section for connected wire	0.75 - 500 mm ²	Halogen	No
Text field height	25.4 mm	Text field width	50.8 mm

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02
ECLASS 14.0	27-28-11-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

THM WO 50.8/150 RT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

THM WO 50.8/150 RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM WO 50.8/150 RT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	