


CC 15/27 K MC NE GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | ClipCard, Device markers, 15 x 27 mm, yellow |
| Order No. | 1131910000 |
| Type | CC 15/27 K MC NE GE |
| GTIN (EAN) | 4032248912285 |
| Qty. | 80 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

CC 15/27 K MC NE GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 1 mm | Depth (inches) | 0.039 inch |
| Height | 15 mm | Height (inches) | 0.591 inch |
| Width | 27 mm | Width (inches) | 1.063 inch |
| Net weight | 1.463 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

General data

| | | | |
|--|------------------------------|-----------|--|
| Adhesive | Double-sided adhesive tape | | |
| Colour | yellow | | |
| Halogen | No | | |
| Material | Polyamide 66 | | |
| Material colour according to resistance code | 4 | | |
| Number of markers per combination | 1 MultiCard = Device markers | | |
| Number of markers per packaging unit | Form of supply | MultiCard | |
| Operating temperature range | -40...60 °C | | |
| Operating temperature range, max. | 60 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Recommended industries | Machinery | | |
| UL 94 flammability rating | V-2 | | |
| Version | Self-adhesive | | |
| Width | 27 mm | | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |
| ECLASS 14.0 | 27-28-11-04 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Engineering Data | CAD data – STEP |
| Product Change Notification | MultiCard Material modification MultiCard Material Modifikation |
| Catalogues | Catalogues in PDF-format |

Creation date August 29, 2024 7:25:44 AM CEST

CC 15/27 K MC NE GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



CC 15/27 K MC NE GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories****General ordering data**

| | | |
|------------|----------------------------|--|
| Type | ETO CC 15/27 TRANSPAR. | Version |
| Order No. | 1880810000 | ClipCard, Accessories, 15 x 27 mm, Transparent |
| GTIN (EAN) | 4032248480890 | |
| Qty. | 10 pc(s). | |