

SCM-I QV S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Cross-connection for the sockets in the D-SERIES DRM.

General ordering data

Version	RIDERSERIES RCM, Cross-connector
Order No.	1132080000
Type	SCM-I QV S
GTIN (EAN)	4032248912193
Qty.	10 pc(s).

SCM-I QV S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	6.5 g
------------	-------

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-45 °C...70 °C
---------------------	----------------	-----------------------	----------------

Cross-connection data

Rated current	12 A	Insulation	Yes
Touch-safe protection	Yes	Colour	white
Number of cross-connected terminals	6	Number of poles	6
Pitch in mm (P)	27 mm	Version	can be cut to length

General data

Version	can be cut to length	Colour	white
---------	----------------------	--------	-------

Connection data

Pitch in mm (P)	27 mm
-----------------	-------

Classifications

ETIM 6.0	EC002586	ETIM 7.0	EC002586
ETIM 8.0	EC002586	ETIM 9.0	EC002586
ECLASS 9.1	27-37-16-92	ECLASS 10.0	27-37-16-92
ECLASS 11.0	27-37-16-92	ECLASS 12.0	27-37-16-92
ECLASS 13.0	27-37-16-92	ECLASS 14.0	27-37-16-92

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

SCM-I QV S


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use

How to install cross connection



Plug the cross connection into wire-connection opening
and fix it with tighten the screw

Plug the cross-connection in the cable connections

Example of use

