

**KT 14****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

**General ordering data**

Version	Cutting tools, Cutting tool for one-hand operation
Order No.	<a href="#">1157820000</a>
Type	KT 14
GTIN (EAN)	4032248945344
Qty.	1 pc(s).

## KT 14

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	30 mm	Depth (inches)	1.181 inch
Height	63.5 mm	Height (inches)	2.5 inch
Width	225 mm	Width (inches)	8.858 inch
Net weight	324.78 g		

## Technical data

Description of article	Cutting tool for up to 14 mm outside diameter	Version	One-hand mechanical
------------------------	---	---------	---------------------

## Cutting tools

Copper cable - flexible, max.	70 mm <sup>2</sup>	Copper cable - flexible, max. (AWG)	2/0 AWG
Copper cable - solid, max.	16 mm <sup>2</sup>	Copper cable - solid, max. (AWG)	6 AWG
Copper cable - stranded, max.	35 mm <sup>2</sup>	Copper cable - stranded, max. (AWG)	2 AWG
Copper cable, max. diameter	14 mm	Data / telephone / control cable, max. Ø	14 mm
Single-core aluminium cable, max.(mm <sup>2</sup> )	35 mm <sup>2</sup>	Stranded aluminium cable, max (mm <sup>2</sup> )	70 mm <sup>2</sup>
Stranded aluminium cable, max. (AWG)	2/0 AWG	Stranded aluminium cable, max. diameter	14 mm

## Classifications

ETIM 6.0	EC000142	ETIM 7.0	EC000142
ETIM 8.0	EC000142	ETIM 9.0	EC000142
ECLASS 9.0	21-04-47-01	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-47-01	ECLASS 11.0	21-04-47-01
ECLASS 12.0	21-04-47-01	ECLASS 13.0	21-04-47-01

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

## Approvals

Approvals



## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Manufacturer's Declaration - Cable cutters</a>
Product Change Notification	<a href="#">Technische Änderung für KT 8, KT 12, KT 14; KT 22</a> <a href="#">Technical change to KT 8, KT 12, KT 14; KT 22</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## KT 14

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



max. 14 mm



max. 16 mm<sup>2</sup>



max. 35 mm<sup>2</sup>



max. 70 mm<sup>2</sup>

suggested cross-section range/  
Empfohlener Querschnittsbereich