

AP MCZ1.5 GN 1670**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Open miniature housing in modular terminal format with five tension clamp connections. A transparent hinged top plate can be used for labelling and provides access to potentiometer and status displays. Plug-in cross-connectors can be used to interconnect the three top connections. A cover plate for closing off the housing is also available.

General ordering data

Version	Small housing, OMNIMATE Housing - TERMINAL-BOX green, End plate, Width: 1.5 mm
Order No.	1161290000
Type	AP MCZ1.5 GN 1670
GTIN (EAN)	4032248950355
Qty.	50 pc(s).

AP MCZ1.5 GN 1670**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	55.85 mm	Height (inches)	2.199 inch
Width	1.5 mm	Width (inches)	0.059 inch
Length	91 mm	Length (inches)	3.583 inch
Net weight	5.972 g		

Material data

Comparative Tracking Index (CTI)	600 ≤ CTI	Insulating material	PA 66/6
Insulating material group	I	UL 94 flammability rating	V-0

General data

Colour	green	Colour chart (similar)	RAL 6032
Encapsulation option	Yes	Protection degree	IP20 in installed state
Rail	TS 35		

Assembly properties

Number of poles	5
-----------------	---

Classifications

ETIM 7.0	EC000886	ETIM 8.0	EC000886
ETIM 9.0	EC001031	ECLASS 11.0	27-14-11-33
ECLASS 12.0	27-14-11-33	ECLASS 13.0	27-19-06-02

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL ANALO.SIGN.CONV. EN MB DEVICE MANUF. EN FL MACHINE SAFETY EN FL 72H SAMPLE SER EN PO OMNIMATE EN

AP MCZ1.5 GN 1670

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

