

SAIE-M23-S-W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

| | |
|------------|--|
| Version | Sensor/Actuator plug-in connector, Built-in plugs, Empty enclosure |
| Order No. | 1169980000 |
| Type | SAIE-M23-S-W |
| GTIN (EAN) | 4032248961962 |
| Qty. | 1 pc(s). |

SAIE-M23-S-W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|------|
| Net weight | 81 g |
|------------|------|

Technical data customisable plug-in connectors

| | | | |
|------------------------------|-------------------|--------------------|-----|
| Housing main material | Copper-zinc alloy | Pollution severity | 3 |
| Protection degree | IP67, IP69K | Shield connection | Yes |
| Temperature range of housing | -40...+125 °C | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000437 | ETIM 7.0 | EC003556 |
| ETIM 8.0 | EC003556 | ETIM 9.0 | EC003556 |
| ECLASS 9.1 | 27-44-02-02 | ECLASS 10.0 | 27-44-02-24 |
| ECLASS 11.0 | 27-44-02-24 | ECLASS 12.0 | 27-44-02-24 |
| ECLASS 13.0 | 27-44-02-24 | | |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E344862 |

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN FL FIELDWIRING EN |


SAIE-M23-S-W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Device connector, male

