

SKMUS M20-W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU SS (stainless steel locknut), Locknut, M 20, 2.2 mm, Stainless steel 1.4404
Order No.	1185690000
Type	SKMUS M20-W
GTIN (EAN)	4050118233742
Qty.	240 pc(s).

SKMUS M20-W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	3.2 mm	Height (inches)	0.126 inch
Net weight	5.031 g		

General information

AF size 1	24 mm	Cable glands	M 20
External thread	M 20	Halogen	halogen-free
Internal thread	M 20	Length of thread	2.2 mm
Material	Stainless steel 1.4404	Pitch of thread	1.5 mm
Thickness	3 mm		

Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ETIM 9.0	EC000940
ECLASS 9.0	27-14-44-24	ECLASS 9.1	27-14-44-24
ECLASS 10.0	27-14-44-24	ECLASS 11.0	27-14-44-24
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format