

**A2LCS/63/M63-M63F-WM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

A2LC type cable glands are suitable for un-armored cable and provide a conduit connection female thread, maintains flameproof Ex d and Increased Safety Ex e explosion protection.

**General ordering data**

Version	A2LC (Klippon unarmored with conduit connection thread, Ex e/d cable gland), Cable glands, straight, M 63 x 1.5, 19 mm, OD min. 49.5 - OD max. 56 mm, Stainless steel 1.4404
Order No.	<a href="#">1187270000</a>
Type	A2LCS/63/M63-M63F-WM
GTIN (EAN)	4050118081190
Qty.	4 pc(s).

Creation date June 28, 2024 8:48:16 PM CEST

Catalogue status 14.06.2024 / We reserve the right to make technical changes.

## A2LCS/63/M63-M63F-WM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	59.8 mm	Height (inches)	2.354 inch
Width	88 mm	Width (inches)	3.465 inch
Length	78.8 mm	Length (inches)	3.102 inch
Net weight	902 g		

## Temperatures

Operating temperature	-50 °C...120 °C
-----------------------	-----------------

## Certificate numbers cable gland

Certificate No. (IECEX)	IECEXTPS16.0004X	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (CCC)	2020322313000069	Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X
Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da		

## General information

AF size 1	80 mm	AF size 2	80 mm
Cable glands	M 63	Conduit thread size (metric)	M63
Explosion protection type	Ex d - flameproof, Ex e - increased safety	External thread	M 63 x 1.5
Halogen	No	Installation guidelines	See assembly instructions
Length of thread	19 mm	Material	Stainless steel 1.4404
O-Ring	Silicone	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Outer cable diameter, max.	56 mm
Outer cable diameter, min.	49.5 mm	Pitch of thread	1.5 mm
Protection degree	IP66, IP68	Seal insert	Silicone
Sealing	Silicone	Silicone	Yes
Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7	Tightening torque	130 Nm

## Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-34
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-04	ECLASS 13.0	27-14-08-04

## Environmental Product Compliance

REACH SVHC	/
------------	---

**A2LCS/63/M63-M63F-WM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">ATEX certification</a> <a href="#">IEC Ex certification</a> <a href="#">CCC approval of Cable glands</a> <a href="#">CE Declaration of conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Notice of installation</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**A2LCS/63/M63-M63F-WM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Stainless Steel lock nuts, natural finish**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	SKMUS M63-W	Version
Order No.	<a href="#">1185740000</a>	SKMU SS (stainless steel locknut), Locknut, M 63, 5.3 mm, Stainless
GTIN (EAN)	4050118269970	steel 1.4404
Qty.	20 pc(s).	

**Nylon flat washer - GWDR**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	GWDR M63-W	Version
Order No.	<a href="#">1185670000</a>	in closed state, M 63, Nylon 6
GTIN (EAN)	4064675423270	
Qty.	10 pc(s).	