

E1XZS/20/M20-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

E1XZ type cable glands are suitable for SWB braided steel wire or STA steel taped armor cable, E1XZ type glands maintain flameproof Ex d and Increased Safety Ex e explosion protection. And the armor clamping provides an electrical bond between the cable armor and the glands.

General ordering data

Version	E1XZ (Klippon double seal SWB/STA armored Ex e/d cable gland), Cable glands, straight, M 20 x 1.5, 16 mm, Braided armouring, Metal foil armouring, 0.9 - 1.25 mm, OD min. 15 - OD max. 21 mm, ID min. 10.00 - ID max. 14.00 mm, Stainless steel 1.4404
Order No.	1188040000
Type	E1XZS/20/M20-WM
GTIN (EAN)	4050118087246
Qty.	24 pc(s).

Creation date June 7, 2024 1:23:47 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

E1XZS/20/M20-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Height	62.5 mm	Height (inches)	2.461 inch
Width	33 mm	Width (inches)	1.299 inch
Length	78.5 mm	Length (inches)	3.091 inch
Net weight	161 g		

Temperatures

Operating temperature	-50 °C...120 °C
-----------------------	-----------------

Certificate numbers cable gland

Certificate No. (IECEX)	IECEXTPS16.0004X	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (CCC)	2020322313000069	Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X
Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da		

General information

AF size 1	30 mm	AF size 2	30 mm
Armour, max.	1.25 mm	Armour, min.	0.9 mm
Cable glands	M 20	Explosion protection type	Ex d - flameproof, Ex e - increased safety
External thread	M 20 x 1.5	Halogen	No
Inner cable diameter, max.	14 mm	Inner cable diameter, min.	10 mm
Installation guidelines	See assembly instructions	Length of thread	16 mm
Material	Stainless steel 1.4404	Number of wires	1
O-Ring	Silicone	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Outer cable diameter, max.	21 mm
Outer cable diameter, min.	15 mm	Pitch of thread	1.5 mm
Protection degree	IP66, IP68	Seal insert	Silicone
Sealing	Silicone	Silicone	Yes
Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7	Tightening torque	35 Nm
Type of armouring	Braided armouring, Metal foil armouring	Type of armouring, short term	SWB, STA

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-34
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-04	ECLASS 13.0	27-14-08-04

E1XZS/20/M20-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	ATEX certification IEC Ex certification CCC approval of Cable glands CE Declaration of conformity CE Declaration of conformity
Engineering Data	CAD data – STEP
User Documentation	Notice of installation
Catalogues	Catalogues in PDF-format

E1XZS/20/M20-WM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Nylon flat washer - GWDR**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M20-W	Version
Order No.	1185610000	in closed state, M 20, Nylon 6
GTIN (EAN)	4050118078305	
Qty.	100 pc(s).	

Stainless Steel lock nuts, natural finish

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMUS M20-W	Version
Order No.	1185690000	SKMU SS (stainless steel locknut), Locknut, M 20, 2.2 mm, Stainless
GTIN (EAN)	4050118233742	steel 1.4404
Qty.	240 pc(s).	