

VP NPT1-1/4-EX W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VP series stopping plugs provide a method of filling unused entries in Ex equipment while maintaining Flame-proof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

General ordering data

Version	VP (Klippon Ex blanking plug with mushroom head), Blanking plug, straight, 1 1/4" NPT, 20 mm, Brass, nickel-plated
Order No.	1188570000
Type	VP NPT1-1/4-EX W
GTIN (EAN)	4050118075526
Qty.	12 pc(s).

VP NPT1-1/4-EX W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	20 mm	Height (inches)	0.787 inch
Width	41.9 mm	Width (inches)	1.65 inch
Length	20 mm	Length (inches)	0.787 inch
Diameter	1.25 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	19 mm	Net weight	287 g

Temperatures

Operating temperature	-50 °C...120 °C
-----------------------	-----------------

Certificate numbers cable gland

Certificate No. (IECEX)	IECEXTPS16.0004X	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (CCC)	2020322313000069	Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X
Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da		

General information

Cable glands	NPT 1-1/4"	Diameter of sealing ring	1.25 mm
Explosion protection type	Ex d - flameproof, Ex e - increased safety	External thread	1 1/4" NPT
Halogen	halogen-free	Impact resistance	7.00 J
Installation guidelines	See assembly instructions	Length of thread	20 mm
Material	Brass, nickel-plated	O-Ring	Silicone
Protection degree	IP66, IP68	Silicone	Yes
Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7	Tightening torque	113 Nm

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-35
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	OcOedf9f-b35a-4d1f-b8f0-99d4b22ac203
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

VP NPT1-1/4-EX W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	ATEX certification
	IEC Ex certification
	CCC approval of Cable glands
	CE Declaration of conformity
Engineering Data	CE Declaration of conformity
	CAD data – STEP
User Documentation	Notice of installation
Catalogues	Catalogues in PDF-format