

**VPS M63-EX W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

VP series stopping plugs provide a method of filling unused entries in Ex equipment while maintaining Flame-proof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

**General ordering data**

Version	VP (Klippon Ex blanking plug with mushroom head), Blanking plug, straight, M 63 x 1.5, 16 mm, Stainless steel 1.4404
Order No.	<a href="#">1188750000</a>
Type	VPS M63-EX W
GTIN (EAN)	4050118237153
Qty.	4 pc(s).

## VPS M63-EX W

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	21.5 mm	Height (inches)	0.846 inch
Width	72 mm	Width (inches)	2.835 inch
Length	21.5 mm	Length (inches)	0.846 inch
Diameter	63 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	15 mm	Net weight	511.52 g

## Temperatures

Operating temperature	-50 °C... 120 °C
-----------------------	------------------

## Certificate numbers cable gland

Certificate No. (IECEX)	IECEXTPS16.0004X	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (CCC)	2020322313000069	Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X
Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da		

## General information

Cable glands	M 63	Diameter of sealing ring	63 mm
Explosion protection type	Ex d - flameproof, Ex e - increased safety	External thread	M 63 x 1.5
Halogen	halogen-free	Head diameter	72 mm
Hexagon socket	19 mm	Impact resistance	7.00 J
Installation guidelines	See assembly instructions	Length of thread	16 mm
Material	Stainless steel 1.4404	O-Ring	Silicone
Pitch of thread	1.5 mm	Protection degree	IP66, IP68
Silicone		Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7
	Yes		
Tightening torque	115 Nm		

## Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-35
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

## Approvals

Approvals



ROHS

Conform

## VPS M63-EX W

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">ATEX certification</a>
	<a href="#">IEC Ex certification</a>
	<a href="#">CCC approval of Cable glands</a>
	<a href="#">CE Declaration of conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Notice of installation</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## VPS M63-EX W

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Nylon flat washer - GWDR



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	GWDR M63-W	Version
Order No.	<a href="#">1185670000</a>	in closed state, M 63, Nylon 6
GTIN (EAN)	4064675423270	
Qty.	10 pc(s).	

## Stainless Steel lock nuts, natural finish



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	SKMUS M63-W	Version
Order No.	<a href="#">1185740000</a>	SKMU SS (stainless steel locknut), Locknut, M 63, 5.3 mm, Stainless
GTIN (EAN)	4050118269970	steel 1.4404
Qty.	20 pc(s).	