

**VPS NPT1/2-EX W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

VP series stopping plugs provide a method of filling unused entries in Ex equipment while maintaining Flame-proof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

**General ordering data**

Version	VP (Klippon Ex blanking plug with mushroom head), Blanking plug, straight, 1/2" NPT, 15.5 mm, Stainless steel 1.4404
Order No.	<a href="#">1188760000</a>
Type	VPS NPT1/2-EX W
GTIN (EAN)	4050118237146
Qty.	24 pc(s).

Creation date May 23, 2024 6:12:12 AM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

## VPS NPT1/2-EX W

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	15.5 mm	Height (inches)	0.61 inch
Width	21 mm	Width (inches)	0.827 inch
Length	15.5 mm	Length (inches)	0.61 inch
Diameter	0.5 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	14.5 mm	Net weight	52.4 g

## Temperatures

Operating temperature	-50 °C... 120 °C
-----------------------	------------------

## Certificate numbers cable gland

Certificate No. (IECEX)	IECEXTPS16.0004X	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (CCC)	2020322313000069	Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X
Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da		

## General information

Cable glands	NPT 1/2"	Diameter of sealing ring	0.5 mm
Explosion protection type	Ex d - flameproof, Ex e - increased safety	External thread	1/2" NPT
Halogen	halogen-free	Hexagon socket	10 mm
Impact resistance	7.00 J	Installation guidelines	See assembly instructions
Length of thread	15.5 mm	Material	Stainless steel 1.4404
O-Ring	Silicone	Protection degree	IP66, IP68
Silicone		Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7
	Yes		
Tightening torque	90 Nm		

## Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-35
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

## Approvals

Approvals



ROHS

Conform

## VPS NPT1/2-EX W

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">ATEX certification</a>
	<a href="#">IEC Ex certification</a>
	<a href="#">CCC approval of Cable glands</a>
	<a href="#">CE Declaration of conformity</a>
	<a href="#">CE Declaration of conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Notice of installation</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>