

KLBUE 15-32 FM4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the TS 35 DIN rail. The shield is diverted from the shield clamping saddles via the mounting foot to the TS 35 mounting rail and thus to PE (ground).

General ordering data

Version	Clamping yoke, Clamping yoke
Order No.	1252490000
Type	KLBUE 15-32 FM4
GTIN (EAN)	4032248112524
Qty.	10 pc(s).

KLBUE 15-32 FM4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	64 mm	Depth (inches)	2.52 inch
Height	50.5 mm	Height (inches)	1.988 inch
Width	34.5 mm	Width (inches)	1.358 inch
Net weight	82.4 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Colour	silver
--------	--------

System specifications

Rail	TS 35
------	-------

Additional technical data

Explosion-tested version	No
--------------------------	----

Conductors for clamping (rated connection)

Cable diameter, max.	32 mm	Cable diameter, min.	15 mm
----------------------	-------	----------------------	-------

General

Rail	TS 35
------	-------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ECLASS 9.0	27-14-11-50	ECLASS 9.1	27-14-11-50
ECLASS 10.0	27-14-11-50	ECLASS 11.0	27-14-11-50
ECLASS 12.0	27-14-11-50	ECLASS 13.0	27-25-01-20

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	