

**KLBUE 15-32 CPF16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the C-profiles. The shield is diverted from the shield clamping saddles via the mounting foot to the C-profiles and thus to PE (ground).

**General ordering data**

Version	Clamping yoke, Clamping yoke for shield connection
Order No.	<a href="#">1252540000</a>
Type	KLBUE 15-32 CPF16
GTIN (EAN)	4050118104424
Qty.	10 pc(s).

**KLBUE 15-32 CPF16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	64 mm	Depth (inches)	2.52 inch
Height	32 mm	Height (inches)	1.26 inch
Width	34.5 mm	Width (inches)	1.358 inch
Mounting dimension - width	33.5 mm	Net weight	91.4 g

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Colour	grey
--------	------

**System specifications**

Rail	TS 27
------	-------

**Additional technical data**

Explosion-tested version	No
--------------------------	----

**Conductors for clamping (rated connection)**

Cable diameter, max.	32 mm	Cable diameter, min.	15 mm
----------------------	-------	----------------------	-------

**General**

Rail	TS 27
------	-------

**Classifications**

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ECLASS 9.0	27-14-11-50	ECLASS 9.1	27-14-11-50
ECLASS 10.0	27-14-11-50	ECLASS 11.0	27-14-11-50
ECLASS 12.0	27-14-11-50	ECLASS 13.0	27-25-01-20

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Beipackzettel_KLBUE.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	