

**KTB GP XX3815 AB S4 6MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Abbildung ähnlich

**Integrate, expand and customise: The ideal expansion for every application**

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

**Flange plates**

Flange plates in two thicknesses, for easy replacement of pre-assembl

**General ordering data**

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 376 mm, Width: 117 mm, Depth: 6 mm, Gland plates: top, Bottom, Material: Stainless steel 1.4404, electropolished, silver
Order No.	<a href="#">1256480000</a>
Type	KTB GP XX3815 AB S4 6MM
GTIN (EAN)	4050118093865
Qty.	1 pc(s).

**KTB GP XX3815 AB S4 6MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	6 mm	Depth (inches)	0.236 inch
Height	376 mm	Height (inches)	14.803 inch
Width	117 mm	Width (inches)	4.606 inch
Net weight	2,100 g		

**General information**

Gland plates	top, Bottom	Material	Stainless steel 1.4404
Material thickness	6 mm	Protection class (UL)	Type 3, Type 4X, Type 12
Surface finish	electropolished		

**General information on accessories**

Material	Stainless steel 1.4404	Material thickness	6 mm
Surface finish	electropolished		

**Classifications**

ETIM 6.0	EC000211	ETIM 7.0	EC000211
ETIM 8.0	EC000211	ETIM 9.0	EC000211
ECLASS 9.0	27-14-24-21	ECLASS 9.1	27-18-92-90
ECLASS 10.0	27-14-24-21	ECLASS 11.0	27-14-24-21
ECLASS 12.0	27-14-24-21	ECLASS 13.0	27-14-24-21

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	