

**ADAP M32-NPT1-1/4-W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

ADAP series adaptors provide flexibility and versatility in filling unused entries in Ex equipment while maintaining Flameproof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

**General ordering data**

Version	ADAP (Klippon Ex adaptor), Adapter, straight, M 32 , 1 1/4" NPT, Brass, nickel-plated
Order No.	<a href="#">1262940000</a>
Type	ADAP M32-NPT1-1/4-W
GTIN (EAN)	4050118088816
Qty.	12 pc(s).

**ADAP M32-NPT1-1/4-W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Width	51 mm	Width (inches)	2.008 inch
Length	39 mm	Length (inches)	1.535 inch
Net weight	183 g		

**Temperatures**

Operating temperature	-50 °C...120 °C
-----------------------	-----------------

**Certificate numbers cable gland**

Certificate No. (IECEX)	IECEXTPS16.0004X	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (CCC)	2020322313000069	Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X
Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da		

**General information**

AF size 1	46 mm	Cable glands	M 32
Explosion protection type	Ex d - flameproof, Ex e - increased safety	External thread	M 32
Halogen	halogen-free	Installation guidelines	See assembly instructions
Internal thread	1 1/4" NPT	Length of thread	16 mm
Material	Brass, nickel-plated	O-Ring	Silicone
Operating temperature range, max.	120 °C	Operating temperature range, min.	-50 °C
Outer cable diameter, max.	24 mm	Outer cable diameter, min.	1 mm
Pitch of thread	1.5 mm	Protection degree	IP66
Silicone		Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3
	Yes		
Tightening torque	65 Nm		

**Classifications**

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-06	ECLASS 13.0	27-14-08-06
ECLASS 14.0	27-14-08-06		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	69c399a3-d29f-4fa4-b22e-340c0db02257
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

## ADAP M32-NPT1-1/4-W

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



ROHS

Conform

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">ATEX certification</a> <a href="#">IEC Ex certification</a> <a href="#">CCC approval of Cable glands</a> <a href="#">CE Declaration of conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Notice of installation</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**ADAP M32-NPT1-1/4-W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Brass lock nuts, nickel-plated**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	SKMU M32 MS	Version
Order No.	<a href="#">1737020000</a>	SKMU MS (brass locknut), Locknut, M 32, 4 mm, Brass, nickel-plated
GTIN (EAN)	4008190956493	
Qty.	100 pc(s).	

**Nylon flat washer - GWDR**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	GWDR M32-W	Version
Order No.	<a href="#">1185630000</a>	in closed state, M 32, Nylon 6
GTIN (EAN)	4050118078329	
Qty.	160 pc(s).	