

ADAP M50-NPT1-1/2-W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

ADAP series adaptors provide flexibility and versatility in filling unused entries in Ex equipment while maintaining Flameproof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

General ordering data

| | |
|------------|---|
| Version | ADAP (Klippon Ex adaptor), Adapter, straight, M 50 , 1 1/2" NPT, Brass, nickel-plated |
| Order No. | 1263010000 |
| Type | ADAP M50-NPT1-1/2-W |
| GTIN (EAN) | 4050118088885 |
| Qty. | 6 pc(s). |

ADAP M50-NPT1-1/2-W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Width | 66.5 mm | Width (inches) | 2.618 inch |
| Length | 39 mm | Length (inches) | 1.535 inch |
| Net weight | 320 g | | |

Temperatures

| | |
|-----------------------|-----------------|
| Operating temperature | -50 °C...120 °C |
|-----------------------|-----------------|

Certificate numbers cable gland

| | | | |
|-----------------------------------|---|-------------------------------------|--------------------|
| Certificate No. (IECEX) | IECEXTPS16.0004X | Certificate no. cable gland (ATEX) | TÜV IT 16ATEX 059X |
| Certificate no. cable gland (CCC) | 2020322313000069 | Certificate no. cable gland (IECEX) | IECEX TPS 16.0004X |
| Identification | II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da | | |

General information

| | | | |
|-----------------------------------|--|-----------------------------------|---|
| AF size 1 | 60 mm | Cable glands | M 50 |
| Explosion protection type | Ex d - flameproof, Ex e - increased safety | External thread | M 50 |
| Halogen | halogen-free | Installation guidelines | See assembly instructions |
| Internal thread | 1 1/2" NPT | Length of thread | 16 mm |
| Material | Brass, nickel-plated | O-Ring | Silicone |
| Operating temperature range, max. | 120 °C | Operating temperature range, min. | -50 °C |
| Outer cable diameter, max. | 41 mm | Outer cable diameter, min. | 1 mm |
| Pitch of thread | 1.5 mm | Protection degree | IP66 |
| Silicone | | Standards | EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3 |
| | Yes | | |
| Tightening torque | 100 Nm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000441 | ETIM 7.0 | EC000441 |
| ETIM 8.0 | EC000441 | ETIM 9.0 | EC000441 |
| ECLASS 9.0 | 27-14-44-32 | ECLASS 9.1 | 27-14-44-90 |
| ECLASS 10.0 | 27-14-44-32 | ECLASS 11.0 | 27-14-44-32 |
| ECLASS 12.0 | 27-14-08-06 | ECLASS 13.0 | 27-14-08-06 |
| ECLASS 14.0 | 27-14-08-06 | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 69c399a3-d29f-4fa4-b22e-340c0db02257 |
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |

ADAP M50-NPT1-1/2-W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | ATEX certification IEC Ex certification CCC approval of Cable glands CE Declaration of conformity |
| Engineering Data | CAD data – STEP |
| User Documentation | Notice of installation |
| Catalogues | Catalogues in PDF-format |

ADAP M50-NPT1-1/2-W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Brass lock nuts, nickel-plated**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SKMU M50 MS | Version |
| Order No. | 1737040000 | SKMU MS (brass locknut), Locknut, M 50, 5 mm, Brass, nickel-plated |
| GTIN (EAN) | 4008190956516 | |
| Qty. | 25 pc(s). | |

Nylon flat washer - GWDR

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | | |
|------------|----------------------------|--------------------------------|
| Type | GWDR M50-W | Version |
| Order No. | 1185650000 | in closed state, M 50, Nylon 6 |
| GTIN (EAN) | 4050118078312 | |
| Qty. | 25 pc(s). | |