

ADAP NPT1-M32-W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

ADAP series adaptors provide flexibility and versatility in filling unused entries in Ex equipment while maintaining Flameproof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

General ordering data

Version	ADAP (Klippon Ex adaptor), Adapter, straight, 1" NPT ,M 32, Brass, nickel-plated
Order No.	1263210000
Type	ADAP NPT1-M32-W
GTIN (EAN)	4050118089356
Qty.	12 pc(s).

ADAP NPT1-M32-W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	41.5 mm	Width (inches)	1.634 inch
Length	39 mm	Length (inches)	1.535 inch
Net weight	130 g		

Temperatures

Operating temperature	-50 °C...120 °C
-----------------------	-----------------

Certificate numbers cable gland

Certificate No. (IECEX)	IECEXTPS16.0004X	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (CCC)	2020322313000069	Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X
Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da		

General information

AF size 1	38 mm	Cable glands	NPT 1"
Explosion protection type	Ex d - flameproof, Ex e - increased safety	External thread	1" NPT
Halogen	halogen-free	Installation guidelines	See assembly instructions
Internal thread	M 32	Length of thread	16 mm
Material	Brass, nickel-plated	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Outer cable diameter, max.	24 mm
Outer cable diameter, min.	1 mm	Pitch of thread	2.21 mm
Protection degree		Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3
	IP66		
Tightening torque	113 Nm		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-06	ECLASS 13.0	27-14-08-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	69c399a3-d29f-4fa4-b22e-340c0db02257
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

ADAP NPT1-M32-W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	ATEX certification IEC Ex certification CCC approval of Cable glands CE Declaration of conformity
Engineering Data	CAD data – STEP
User Documentation	Notice of installation
Catalogues	Catalogues in PDF-format