

CB 98/2,5 NC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

| | |
|------------|---|
| Version | Cable ties, 2.5 x 98 mm, Polyamide 66, 80 N |
| Order No. | 1278600000 |
| Type | CB 98/2,5 NC |
| GTIN (EAN) | 4008190154554 |
| Qty. | 100 pc(s). |

CB 98/2,5 NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 1.1 mm | Depth (inches) | 0.043 inch |
| Height | 98 mm | Height (inches) | 3.858 inch |
| Width | 2.5 mm | Width (inches) | 0.098 inch |
| Net weight | 0.24 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...85 °C |
|-----------------------------|-------------|

Installation materials

| | | | |
|-----------------------------------|-------|-----------------------------------|--------------|
| Bundle diameter, max. | 21 mm | Bundle diameter, min. | 1 mm |
| Cable diameter, max. | 21 mm | For re-opening | No |
| Halogen | No | Material | Polyamide 66 |
| Operating temperature range, max. | 85 °C | Operating temperature range, min. | -40 °C |
| Tensile strength | 80 N | Tensile strength (Pound-force) | 18 lbf |
| UL 94 flammability rating | V-2 | UV-resistant | No |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000046 | ETIM 7.0 | EC000046 |
| ETIM 8.0 | EC000046 | ETIM 9.0 | EC000046 |
| ECLASS 9.0 | 27-14-07-02 | ECLASS 9.1 | 27-14-07-02 |
| ECLASS 10.0 | 27-14-07-02 | ECLASS 11.0 | 27-14-07-02 |
| ECLASS 12.0 | 27-14-07-02 | ECLASS 13.0 | 27-14-07-02 |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E317499 |

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | DE PI830000 160627 001 |
| Catalogues | Catalogues in PDF-format |

CB 98/2,5 NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

