

**CB 365/7,5 NC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

**General ordering data**

Version	Cable ties, 7.5 x 365 mm, Polyamide 66, 540 N
Order No.	<a href="#">1279100000</a>
Type	CB 365/7,5 NC
GTIN (EAN)	4008190104665
Qty.	100 pc(s).

## CB 365/7,5 NC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0 mm	Height	365 mm
Height (inches)	14.37 inch	Width	7.5 mm
Width (inches)	0.295 inch	Net weight	5.104 g

## Temperatures

Operating temperature range	-40...85 °C
-----------------------------	-------------

## Installation materials

Bundle diameter, max.	100 mm	Bundle diameter, min.	8 mm
Cable diameter, max.	100 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	540 N	Tensile strength (Pound-force)	121 lbf
UL 94 flammability rating	V-2	UV-resistant	No

## Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">DE PI830000 160627 001</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### CB 365/7,5 NC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

