

**KTB GP 26XX20 CD S4 3MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Abbildung ähnlich

**Integrate, expand and customise: The ideal expansion for every application**

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

**Flange plates**

Flange plates in two thicknesses, for easy replacement of pre-assembl

**General ordering data**

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 204 mm, Width: 167 mm, Depth: 3 mm, Gland plates: left, right, Material: Stainless steel 1.4404, electropolished, silver
Order No.	<a href="#">1280940000</a>
Type	KTB GP 26XX20 CD S4 3MM
GTIN (EAN)	4050118071764
Qty.	1 pc(s).

**KTB GP 26XX20 CD S4 3MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	3 mm	Depth (inches)	0.118 inch
Height	204 mm	Height (inches)	8.031 inch
Width	167 mm	Width (inches)	6.575 inch
Net weight	824 g		

**General information**

Gland plates	left, right	Integral fixing	Screwed
Material	Stainless steel 1.4404	Material thickness	3 mm
Protection class (UL)	Type 3, Type 4X, Type 12	Surface finish	electropolished

**General information on accessories**

Material	Stainless steel 1.4404	Material thickness	3 mm
Surface finish	electropolished		

**Classifications**

ETIM 6.0	EC000211	ETIM 7.0	EC000211
ETIM 8.0	EC000211	ETIM 9.0	EC000211
ECLASS 9.0	27-14-24-21	ECLASS 9.1	27-18-92-90
ECLASS 10.0	27-14-24-21	ECLASS 11.0	27-14-24-21
ECLASS 12.0	27-14-24-21	ECLASS 13.0	27-14-24-21

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--