

CC-M 27/18 ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|---|
| Version | MetalliCard, Device markers, 26.8 x 18 mm, silver |
| Order No. | 1327640000 |
| Type | CC-M 27/18 ST |
| GTIN (EAN) | 4050118132533 |
| Qty. | 200 pc(s). |

CC-M 27/18 ST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.5 mm | Depth (inches) | 0.02 inch |
| Height | 26.8 mm | Height (inches) | 1.055 inch |
| Width | 18 mm | Width (inches) | 0.709 inch |
| Net weight | 1.78 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...130 °C |
|-----------------------------|--------------|

General data

| | | |
|--------------------------------------|--------------------------------|-------------|
| Colour | silver | |
| Material | Stainless steel 1.4301 | |
| Number of markers per combination | 1 MetalliCard = Device markers | |
| Number of markers per packaging unit | Form of supply | MetalliCard |
| Operating temperature range | -55...130 °C | |
| Operating temperature range, max. | 130 °C | |
| Operating temperature range, min. | -55 °C | |
| Recommended industries | Energy, Process | |
| Size of labelling field | 25 x 15 mm | |
| Width | 18 mm | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |

CC-M 27/18 ST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



CC-M 27/18 ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Complementary products****General ordering data**

Type INLAY CC-M UNIVERSAL

Order No. [1341120000](#)

GTIN (EAN) 4050118145458

Qty. 1 pc(s).

Type PRIMER CC-M

Order No. [2068020000](#)

GTIN (EAN) 4050118416534

Qty. 100 pc(s).

Type DKB CC 27/18

Version

Order No. [1341140000](#)

MetalliCard, Adhesive strip, 27 x 18 mm, Transparent

GTIN (EAN) 4050118145625

Qty. 320 pc(s).

Type INLAY CC-M 27/18

Order No. [1341040000](#)

GTIN (EAN) 4050118145397

Qty. 1 pc(s).