

INLAY CC-M 85/54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Order No.	1341030000
Type	INLAY CC-M 85/54
GTIN (EAN)	4050118145427
Qty.	1 pc(s).

INLAY CC-M 85/54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	120 mm	Depth (inches)	4.724 inch
Height	8 mm	Height (inches)	0.315 inch
Width	76 mm	Width (inches)	2.992 inch
Net weight	50 g		

General data

Version	Holder for 1 sign	Width	76 mm
---------	-------------------	-------	-------

Classifications

ETIM 6.0	EC001675	ETIM 7.0	EC001675
ETIM 8.0	EC001675	ETIM 9.0	EC001675
ECLASS 9.0	19-14-92-90	ECLASS 9.1	19-14-92-90
ECLASS 10.0	19-14-92-90	ECLASS 11.0	19-14-90-90
ECLASS 12.0	19-14-90-90	ECLASS 13.0	19-14-90-90

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

INLAY CC-M 85/54

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Example of use



INLAY CC-M 85/54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Standard**

MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	CC-M 85/54 AL	Version
Order No.	1327600000	MetalliCard, Device markers, 54 x 85 mm, silver
GTIN (EAN)	4050118132502	
Qty.	40 pc(s).	
Type	CC-M 85/54 ST	Version
Order No.	1327620000	MetalliCard, Device markers, 54 x 85 mm, silver
GTIN (EAN)	4050118132519	
Qty.	40 pc(s).	

INLAY CC-M 85/54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****With hole**

MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	CC-M 85/54 4X3 AL	Version
Order No.	1327800000	MetalliCard, Device markers, 54 x 85 mm, silver
GTIN (EAN)	4050118132663	
Qty.	40 pc(s).	
Type	CC-M 85/54 4X3 ST	Version
Order No.	1327820000	MetalliCard, Device markers, 54 x 85 mm, silver
GTIN (EAN)	4050118132670	
Qty.	40 pc(s).	