

PAC-UNIV-HE40-F-6M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

General ordering data

| | |
|------------|----------------------------|
| Version | Pre-assembled cable, PAC |
| Order No. | 1349880060 |
| Type | PAC-UNIV-HE40-F-6M |
| GTIN (EAN) | 4032248208159 |
| Qty. | 1 pc(s). |

PAC-UNIV-HE40-F-6M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|---------|
| Net weight | 838.5 g |
|------------|---------|

Temperatures

| | | | |
|---------------------|-------------|-----------------------|----------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 |
|---------------------|-------------|-----------------------|----------|

General Data

| | | | |
|--------------------|--|-----------------------|---------------------------|
| Cable | Cable LiYY | Cable length | 6 |
| Connector PLC side | H0.14/10 (FERRULES 0.14mm ²) | Interface connector | FLAT CABLE PLANO HE10 40P |
| Material | PVC | Number of poles, min. | 40-pole |
| Outer diameter | 11.7 ± 1 mm | Suitable for | Digital signals |
| Wire cross-section | 0.14 mm ² | | |

Electrical Data

| | | | |
|------------------------|---------------------|---|------------|
| Capacity wire / shield | 300 pF/m | Capacity wire / wires | 300 pF/m |
| Operating voltage | ≤ 60 V DC ≤ 25 V AC | Permissible current strength per path, max. | 1 A |
| Rated voltage | ≤ 60 V DC ≤ 25 V AC | Resistance | ≤ 150 mΩ/m |
| Total current, max. | 3 A | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000237 | ETIM 7.0 | EC000237 |
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ECLASS 9.0 | 27-24-22-20 | ECLASS 9.1 | 27-24-22-20 |
| ECLASS 10.0 | 27-24-22-20 | ECLASS 11.0 | 27-24-22-20 |
| ECLASS 12.0 | 27-24-22-20 | ECLASS 13.0 | 27-24-22-20 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|--|
| User Documentation | Colours chart |
| Catalogues | Catalogues in PDF-format |