

VPU II 0 PV 1000V DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Surge voltage arrester, Low voltage, Accessories
Order No.	1351190000
Type	VPU II 0 PV 1000V DC
GTIN (EAN)	4050118158847
Qty.	1 pc(s).

VPU II 0 PV 1000V DC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	64 mm	Depth (inches)	2.52 inch
Height	52 mm	Height (inches)	2.047 inch
Width	17.8 mm	Width (inches)	0.701 inch
Net weight	103 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...
---------------------	----------------	-----------------------	-----------

General data

Colour	orange	Design	Installation housing; 1TE, Insta IP 20
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20
Rail	TS 35	UL 94 flammability rating	V-0

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Photovoltaic technical data

Maximum continuous operating voltage		PV system voltage, max. U_{cpv}	
DC UCPV mode +/-, -/PE, +/-PE	1,000 V		1,000 V
Protection level U_p (+/-, -/PE, +/-PE)	≤ 2.6 kV	Protection level U_p at I_N (per module)	≤ 2.8 kV
Requirements class	Type II	Short-circuit current I_{SCPv}	200 A
Standards	EN 50539-11		

Rated data IEC / EN

Discharge current I_{max} (8/20 μ s) wire-PE	25 kA	Discharge current I_n (8/20 μ s) wire-PE	12.5 kA
Leakage current at U_n	30 μ A	Max. continuous voltage, U_c (DC)	1000 V
Number of poles	1	PV voltage, acc. to IEC 60364-7-712	≤ 1000 V
Protection level U_p at I_N (L/N-PE)	≤ 2.8 kV	Rated voltage (DC)	1000 V
Response time	≤ 25 ns	Standards	EN 50539-11
Voltage type	DC		

Connection data

Type of connection	pluggable
--------------------	-----------

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

VPU II 0 PV 1000V DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Tender specification sheets**

Long specification	Spare arrester consisting of V0 material for surge voltage arrester VPU II 1000 VDC series The pluggable high-performance varistors can be exchanged by trained personnel following a failure. Rated voltage: 1000 VDC for PV systems Type: Weidmüller VPU II 0 PV 1000 VDC Order No.: 1351190000	Short specification	Spare arrester for surge voltage arrester VPU II 1000 V DC series The pluggable high-performance varistors can be swapped by trained personnel following a failure. Rated voltage: 1000 V DC for PV systems Type: Weidmüller VPU II 0 PV 1000 V DC Order no.: 1351190000
--------------------	---	---------------------	--

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[EU_Konformitätserklärung / EU_Declaration_of_Conformity](#)

User Documentation

[Beipackzettel / Instruction sheet](#)

Catalogues


[Catalogues in PDF-format](#)

VPU II 0 PV 1000V DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



VPU II 0 PV 1000V DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Slotted screwdriver**

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Type	SDIS 1.0X5.5X125	Version
Order No.	2749850000	Screwdriver, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade
GTIN (EAN)	4050118897050	thickness (A): 1 mm
Qty.	1 pc(s).	

Crosshead screwdriver Phillips

VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Type	SDIK PH1 X 80	Version
Order No.	2749890000	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
GTIN (EAN)	4050118897098	
Qty.	1 pc(s).	