

**HEVB ASK1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The lever link provides a mechanical connection of two separating levers.

**General ordering data**

Version	Operating tool, Lever connector
Order No.	<a href="#">1359500000</a>
Type	HEVB ASK1
GTIN (EAN)	4008190039967
Qty.	50 pc(s).

**HEVB ASK1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	3.17 mm	Depth (inches)	0.125 inch
Height	8.2 mm	Height (inches)	0.323 inch
Width	15 mm	Width (inches)	0.591 inch
Net weight	0.3 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50
Continuous operating temp., max.	100		

**Material data**

Material	PA 66	Colour	black
----------	-------	--------	-------

**Additional technical data**

Installation advice	Direct mounting
---------------------	-----------------

**General**

Installation advice	Direct mounting
---------------------	-----------------

**Classifications**

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-04-50-03
ECLASS 12.0	21-04-50-03	ECLASS 13.0	21-04-50-03

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>