

THM WO VIN 24.5/100 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 8 - 23 mm, 24.5 x 100 mm, white
Order No.	1391430000
Type	THM WO VIN 24.5/100 WS
GTIN (EAN)	4050118191714
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

THM WO VIN 24.5/100 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.065 mm	Depth (inches)	0.003 inch
Height	24.5 mm	Height (inches)	0.965 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	994 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Adhesive	Polyacrylate adhesive	
Approval acc. to UL 969	No	
Colour	white	
Halogen	Yes	
Material	Vinyl film	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Label reel
Number per roll	2,000	
Operating temperature range	-40...80 °C	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Size of labelling field	25 x 24.5 mm	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Version	Self-adhesive	
Width	100 mm	

Conductor and cable markers

Conductor O.D.	8 - 23 mm	Conductor O.D., max.	23 mm
Conductor O.D., min.	8 mm	Conductor cross-section, max.	95 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 95 mm ²
Halogen	Yes	Text field height	25 mm
Text field width	24.5 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

THM WO VIN 24.5/100 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues


[Catalogues in PDF-format](#)

THM WO VIN 24.5/100 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM WO VIN 24.5/100 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	