

**INLAY CC-M 70/48****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Order No.	<a href="#">1415940000</a>
Type	INLAY CC-M 70/48
GTIN (EAN)	4050118217247
Qty.	1 pc(s).

**INLAY CC-M 70/48****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	120 mm	Depth (inches)	4.724 inch
Height	8 mm	Height (inches)	0.315 inch
Width	76 mm	Width (inches)	2.992 inch
Net weight	65 g		

**General data**

Operating temperature range, max.	130 °C	Operating temperature range, min.	-55 °C
Version	Holder for 3 signs	Width	76 mm

**Classifications**

ETIM 6.0	EC001675	ETIM 7.0	EC001675
ETIM 8.0	EC001675	ETIM 9.0	EC001675
ECLASS 9.0	19-14-92-90	ECLASS 9.1	19-14-92-90
ECLASS 10.0	19-14-92-90	ECLASS 11.0	19-14-90-90
ECLASS 12.0	19-14-90-90	ECLASS 13.0	19-14-90-90

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

### INLAY CC-M 70/48

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use

