

HSS-HF 1.2-2.4 EL Y13M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 1.2 - 2.4 mm, yellow
Order No.	1423220000
Type	HSS-HF 1.2-2.4 EL Y13M
GTIN (EAN)	4050118227628
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

HSS-HF 1.2-2.4 EL Y13M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.02 inch
Width	4.2 mm	Width (inches)	0.165 inch
Length	13,000 mm	Length (inches)	511.81 inch
Net weight	86 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

General data

Colour	yellow	Halogen	No
Length	13,000 mm	Material	Polyolefine
Number per roll	1	Operating temperature range	-55...105 °C
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Printed characters	without	Type of printing	neutral
Width	4.2 mm		

Conductor and cable markers

Conductor O.D.	1.2 - 2.4 mm	Conductor O.D., max.	2.4 mm
Conductor O.D., min.	1.2 mm	Conductor cross-section, max.	0.5 mm ²
Conductor cross-section, min.	0.25 mm ²	Cross-section for connected wire	0.25 - 0.5 mm ²
Halogen	No	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Text field height	4 mm
Text field width	0 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN ISO 4589-2 1999 EN 45545-2:2020
Catalogues	Catalogues in PDF-format

HSS-HF 1.2-2.4 EL Y13M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HSS-HF 1.2-2.4 EL Y13M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****THM MULTIMARK**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	THM MMP ROLLER 115
Order No.	1357420000
GTIN (EAN)	4050118160314
Qty.	1 pc(s).

Type	THM MMP ROLLER 30
Order No.	1357430000
GTIN (EAN)	4050118160253
Qty.	1 pc(s).

Ink ribbons

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON HSS HF EL 40/300 ...	Version
Order No.	1426210000	Ink ribbon
GTIN (EAN)	4050118228823	
Qty.	1 pc(s).	

HSS-HF 1.2-2.4 EL Y13M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MM PLUS ROLLER 110
Order No.	2672590000
GTIN (EAN)	4050118708097
Qty.	1 pc(s).