

RIBBON HSS HF EL 40/300 SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Version	Ink ribbon
Order No.	1426210000
Type	RIBBON HSS HF EL 40/300 SW
GTIN (EAN)	4050118228823
Qty.	1 pc(s).

RIBBON HSS HF EL 40/300 SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	40 mm	Width (inches)	1.575 inch
Length	300,000 mm	Length (inches)	11,811 inch
Net weight	115 g		

Classifications

ETIM 6.0	EC001694	ETIM 7.0	EC001694
ETIM 8.0	EC001694	ETIM 9.0	EC001694
ECLASS 9.0	19-14-92-90	ECLASS 9.1	19-14-06-11
ECLASS 10.0	19-14-92-90	ECLASS 11.0	19-14-90-90
ECLASS 12.0	19-14-90-90	ECLASS 13.0	19-14-90-90

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--