

IE-FSMZ2LY0005MLD0LD0-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled IE cables, FO

General ordering data

Version	Patch cable, duplex clip included, LC-Duplex IP 20, LC-Duplex IP 20, 9 µm, LSZH, 5 m
Order No.	1433950050
Type	IE-FSMZ2LY0005MLD0LD0-X
GTIN (EAN)	4050118242379
Qty.	1 pc(s).

IE-FSMZ2LY0005MLD0LD0-X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	5 m	Length (inches)	196.85 inch
Net weight	54 g		

Temperatures

Operating temperature	-20 °C...70
-----------------------	-------------

Cable specific standards

Specification for checking the symmetrical communication cabling	IEC 61935-3	Specification for twisted-pair device connection cables	IEC 61156-6, DIN EN 50288-4-2
--	-------------	---	-------------------------------

General standards

Connector standard	IEC 61754-20
--------------------	--------------

Standards

Connector standard	IEC 61754-20
--------------------	--------------

Cable structure

Cable layout	ZIPCORD	Core diameter	9 µm
Material sheath	LSZH	Primary coating	245 µm
Sheath diameter	2.0 * 4.1 mm	Sheathing colour	yellow
Standard designations	I-V(ZN)H		

Mechanical and material properties of cable

Halogen	No	Min. bending radius, once only	20 mm
Min. bending radius, repetitive	40 mm		

Plug

Plug left	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded	Plug right	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
-----------	--	------------	--

Plug, left

Plug left	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
-----------	--

Plug, right

Plug right	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
------------	--

IE-FSMZ2LY0005MLD0LD0-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ETIM 9.0	EC002607
ECLASS 9.0	27-06-10-03	ECLASS 9.1	27-06-10-03
ECLASS 10.0	27-06-10-03	ECLASS 11.0	27-06-10-03
ECLASS 12.0	27-06-10-03	ECLASS 13.0	27-06-10-03

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN


IE-FSMZ2LY0005MLD0LD0-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Detailed drawing



IE-FSMZ2LY0005MLD0LD0-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****V0 material**

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Type	VT SF 6/21 MC NE WS V0	Version
Order No.	1730560001	SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm,
GTIN (EAN)	4008190954611	white
Qty.	160 pc(s).	
Type	VT SF 5/21 MC NE WS V0	Version
Order No.	1689470001	SlimFix, Conductor and cable markers, 4.8 - 7.4 mm, 21 x 7.4 mm,
GTIN (EAN)	4008190872571	white
Qty.	160 pc(s).	