

**GZ 10.0A/F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

For protection against overcurrent, we offer cartridge fuse with dimensions 6.3x32 mm in sizes from 500 mA to 12.5 A.

**General ordering data**

Version	Miniature fuse, quick-acting, 10 A, G-Si. 6.3 x 32
Order No.	<a href="#">1460640000</a>
Type	GZ 10.0A/F
GTIN (EAN)	4050118266801
Qty.	10 pc(s).

**GZ 10.0A/F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	6.3 mm	Depth (inches)	0.248 inch
Height	32 mm	Height (inches)	1.26 inch
Width	6.3 mm	Width (inches)	0.248 inch
Net weight	2.476 g		

**Material data**

Colour	Light Grey
--------	------------

**System specifications**

Version	Fuse accessories
---------	------------------

**Additional technical data**

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

**Fuse cartridges**

Cartridge fuse	G-Si. 6.3 x 32	Characteristics	quick-acting
Colour	Light Grey	Current	10 A
Melting integral	240 A <sup>2</sup> s	Optical function display	No
Power output (@ 1.5 In)	4 W	Rated breaking capacity	1.5 kA
Version	Fuse accessories	Voltage drop	150 mV

**General**

Installation advice	Direct mounting
---------------------	-----------------

**Rating data**

Rated voltage	500 V	Rated current	10 A
---------------	-------	---------------	------

**Classifications**

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ETIM 9.0	EC002704
ECLASS 9.0	27-14-20-01	ECLASS 9.1	27-14-20-01
ECLASS 10.0	27-14-20-01	ECLASS 11.0	27-14-20-01
ECLASS 12.0	27-14-20-01	ECLASS 13.0	27-14-20-01

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	