

SAI-ADAPT-M8/M12 3P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

M8/M12 and M12/M8 adapters serve for quick implementation of the plug size.

General ordering data

Version	Y connector, M8 / M12
Order No.	1473460000
Type	SAI-ADAPT-M8/M12 3P
GTIN (EAN)	4050118279696
Qty.	1 pc(s).

SAI-ADAPT-M8/M12 3P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	15 g
------------	------

Connection data

Single outlet 1 - plug-in connector	M8 pin	Single outlet 2 - plug-in connector	M12 socket
Tightening torque		M12: 0.8 Nm, M8: 0.5 Nm	

Technical data customisable plug-in connectors

Coding	M12 = A-coded, M8 = none	Number of poles	3
Pollution severity	3	Protection degree	IP67
Rated voltage	24 V		

Standards

Connector standard	IEC 61076-2-101, IEC 61076-2-104
--------------------	----------------------------------

General data

Coding	M12 = A-coded, M8 = none	Conductor O.D.	-
Connection thread	M8 / M12	Number of poles	3
Pollution severity	3	Protection degree	IP67
Rated voltage	24 V		

Classifications

ETIM 6.0	EC002925	ETIM 7.0	EC002925
ETIM 8.0	EC002925	ETIM 9.0	EC002925
ECLASS 9.0	27-44-01-06	ECLASS 9.1	27-44-01-06
ECLASS 10.0	27-44-01-06	ECLASS 11.0	27-44-01-06
ECLASS 12.0	27-44-01-06	ECLASS 13.0	27-44-01-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1c533b66-fcff-4da5-b89f-fd55fbf5cb55

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN

Creation date June 3, 2024 1:29:17 PM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.


SAI-ADAPT-M8/M12 3P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Wiring diagram

