

**HDC HP ABGH COVER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The protective housing is manufactured from seawater-resistant aluminium using pressure die casting.

High standards of water and dust protection, as well as particularly high impact resistance, are the hallmarks of this housing series.

A sophisticated two-stage surface coating ensures years of reliability.

All screws, crimp contacts and other exterior accessory parts are made of corrosion-resistant stainless steel.

**General ordering data**

Version	HDC enclosures, Cover
Order No.	<a href="#">1473470000</a>
Type	HDC HP ABGH COVER
GTIN (EAN)	4050118279917
Qty.	1 pc(s).

**HDC HP ABGH COVER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	41.3 mm	Width (inches)	1.626 inch
Diameter	55 mm	Net weight	121 g

**Temperatures**

Limit temperature	-40 °C ... 120 °C
-------------------	-------------------

**Dimensions**

Width	41.3 mm
-------	---------

**General data**

Colour	black (similar to RAL 9005)	Enclosure material	Aluminium diecast
Seal material	EPDM	Series	HighPower
Surface finish	Powder coating	Type	Cover

**Classifications**

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ECLASS 9.0	27-44-02-92	ECLASS 9.1	27-44-01-92
ECLASS 10.0	27-44-02-92	ECLASS 11.0	27-44-02-92
ECLASS 12.0	27-44-02-92	ECLASS 13.0	27-44-02-92

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">58992_HDC_HP_ABGH_COVER_00_BLATT.pdf</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a>