

H0,34/5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in polybag

General ordering data

Version	Wire-end ferrule, Standard, 5 mm, 5 mm, No
Order No.	1475640000
Type	H0,34/5
GTIN (EAN)	4050118282238
Qty.	1,000 pc(s).
Packaging	loose

H0,34/5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	0.023 g
------------	---------

Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Collar diameter (D2)	1.8 mm	Conductor cross-section	0.34 mm ²
Contact surface diameter (D1)	0.85 mm	Contact surface length (L2)	5 mm
L1 in mm	5 mm	Stripping length	5 mm
Wire connection cross section AWG, max.	AWG 22		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

H0,34/5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

