

CA 100 - 2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Orders on request only



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper
Order No.	1476920000
Type	CA 100 - 2.5
GTIN (EAN)	4050118283754
Qty.	1 pc(s).

CA 100 - 2.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	420 mm	Depth (inches)	16.535 inch
Height	425 mm	Height (inches)	16.732 inch
Width	470 mm	Width (inches)	18.504 inch
Net weight	38,000 g		

PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 bar	Consumables	loose cable lugs, with plastic collar
Crimping	Quadrocrimp	Crimping length	6/8/10/12 mm
Drive	Electropneumatic	Electrical connection	100-240 V / 50/65 Hz
Length of wire-end ferrule	12/14/16/18 mm	Pulse time	approx. 1.5 s
Stripping range	0.34 - 4 mm ² (~AWG 22 - 12)	Wire end ferrules cross-section, max.	4 mm ²
Wire end ferrules cross-section, min.	0.34 mm ²		

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-01
ECLASS 10.0	17-13-01-01	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	CA 100 - 2.5 Manual_CA 100 2.5_multiple language
Catalogues	Catalogues in PDF-format

CA 100 - 2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

