

WFSKHV/0,5-1,05**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Insulated cable connector in PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 0.5 mm ² - 1 mm ²
Order No.	1491960000
Type	WFSKHV/0,5-1,05
GTIN (EAN)	4050118301977
Qty.	100 pc(s).

WFSKHV/0,5-1,05**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	1.26 g
------------	--------

Connectors

Conductor cross-section, max.	1 mm ²	Conductor cross-section, min.	0.5 mm ²
Identification colour	red	Insulation	Fully insulated
Length 1 (l1)	16.3 mm	Material/plastic	PA
Plug-in density (d3)	0.8 mm	Plug-in width (d2)	6.3 mm

Classifications

ETIM 6.0	EC000516	ETIM 7.0	EC000516
ETIM 8.0	EC000516	ETIM 9.0	EC000516
ECLASS 9.0	27-44-03-92	ECLASS 9.1	27-40-02-90
ECLASS 10.0	27-44-03-92	ECLASS 11.0	27-44-03-92
ECLASS 12.0	27-44-03-92	ECLASS 13.0	27-44-03-92

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

WFSKHV/0,5-1,05

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

