

KQI-M4/-2,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Insulated cable connector in PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² - 2.5 mm ²
Order No.	1492290000
Type	KQI-M4/-2,5
GTIN (EAN)	4050118302172
Qty.	100 pc(s).

KQI-M4/-2,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	0.91 g
------------	--------

Connectors

Conductor cross-section	2.5 mm ²	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	1.5 mm ²	Connection length (l)	18 mm
Hole	M 4	Identification colour	blue
Inside diameter of collar (d4)	4.4 mm	Inside diameter of flange (d2)	4.3 mm
Inside diameter of shaft (d1)	2.3 mm	Insulation	Available
Material/plastic	PC	Outside diameter of shaft (d3)	8 mm

Classifications

ETIM 6.0	EC001059	ETIM 7.0	EC001059
ETIM 8.0	EC001059	ETIM 9.0	EC001059
ECLASS 9.0	27-40-02-12	ECLASS 9.1	27-40-02-12
ECLASS 10.0	27-40-02-12	ECLASS 11.0	27-40-02-12
ECLASS 12.0	27-40-02-12	ECLASS 13.0	27-40-02-12

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

KQI-M4/-2,5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

