

**KQI-M10/-10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Insulated cable connector in PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

**General ordering data**

Version	cable lug, terminal end, Insulated cable connector, 10 mm <sup>2</sup> , 10 mm <sup>2</sup> - 10 mm <sup>2</sup>
Order No.	<a href="#">1492470000</a>
Type	KQI-M10/-10
GTIN (EAN)	4050118302233
Qty.	50 pc(s).

**KQI-M10/-10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	4 g
------------	-----

**Connectors**

Conductor cross-section	10 mm <sup>2</sup>	Conductor cross-section, max.	10 mm <sup>2</sup>
Conductor cross-section, min.	10 mm <sup>2</sup>	Connection length (l)	29.5 mm
Hole	M10	Identification colour	red
Inside diameter of collar (d4)	8 mm	Inside diameter of flange (d2)	10.5 mm
Inside diameter of shaft (d1)	4.5 mm	Insulation	Available
Material/plastic	PA	Outside diameter of shaft (d3)	18 mm

**Classifications**

ETIM 6.0	EC001059	ETIM 7.0	EC001059
ETIM 8.0	EC001059	ETIM 9.0	EC001059
ECLASS 9.0	27-40-02-12	ECLASS 9.1	27-40-02-12
ECLASS 10.0	27-40-02-12	ECLASS 11.0	27-40-02-12
ECLASS 12.0	27-40-02-12	ECLASS 13.0	27-40-02-12

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## KQI-M10/-10

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

