

**KRN-M20/-185****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

|            |  |
|------------|--|
| Version    | cable lug, terminal end, 185 mm <sup>2</sup> |
| Order No.  | <a href="#">1495470000</a>                   |
| Type       | KRN-M20/-185                                 |
| GTIN (EAN) | 4050118305005                                |
| Qty.       | 25 pc(s).                                    |

**KRN-M20/-185****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |
|------------|----------|
| Net weight | 116.28 g |
|------------|----------|

**Technical data**

|         |                       |
|---------|-----------------------|
| Version | Euro series, standard |
|---------|-----------------------|

**Connectors**

|                                |                     |                                |       |
|--------------------------------|---------------------|--------------------------------|-------|
| Conductor cross-section        | 185 mm <sup>2</sup> | Connection length (l)          | 66 mm |
| Flange width (b)               | 35 mm               | Hole                           | M 20  |
| Inside diameter of flange (d2) | 21 mm               | Inside diameter of shaft (d1)  | 19 mm |
| Insulation                     | not available       | Outside diameter of shaft (d3) | 24 mm |
| Shaft length (a)               | 30 mm               |                                |       |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001051    | ETIM 7.0    | EC001051    |
| ETIM 8.0    | EC001051    | ETIM 9.0    | EC001051    |
| ECLASS 9.0  | 27-40-02-05 | ECLASS 9.1  | 27-40-02-05 |
| ECLASS 10.0 | 27-40-02-05 | ECLASS 11.0 | 27-40-02-05 |
| ECLASS 12.0 | 27-40-02-05 | ECLASS 13.0 | 27-40-02-05 |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |

## KRN-M20/-185

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

